

WonderMASK® PX

Fast-Dry Peelable Solder Mask
2222

Introduction


WonderMASK® PX is a temporary, peelable, latex solder mask designed to dry in half the time of standard peelable solder masks. It is hand applied and can withstand fluxing, wave soldering and cleaning operations. It effectively masks and protects open through-holes and underside components in a wave soldering process, and can be used as a conformal coatings mask.

WonderMASK PX can remain on all areas of the board until ready for test, and then, be easily peeled away. In addition, WonderMASK PX is ideally suited for situations where a thick coat of mask is required. WonderMASK PX has been specially formulated to cure homogenously, virtually eliminating any limit on the deposition thickness.

Features / Benefits

- Fast Drying – dries in half the time of standard peelable masks
- Ideal for situations where a thick coat of mask is required
- Peelable Mask
- Able to withstand temperatures up to 650°F / 343°C
- Prevents solder from flowing into contacts, terminals, screw heads, and plated through holes
- Mask for conformal coating
- Will not tarnish gold or phosphor bronze
- Protects delicate components

WonderMASK PX is not recommended for use on bare copper as it contains a sufficient concentration of ammonia to cause discoloration. For use on bare copper, WonderMASK PL (part # 2211) is recommended.



**Dry time is the time until the mask could be easily removed, in one piece, from the substrate. Beads of mask were approximately 4 inches in length.*

Directions

- Apply mask to areas that you do not want soldered
- Allow mask to cure (cure time is dependent on thickness of mask applied and environmental conditions, e.g. temperature, humidity)
- Send board onto solder stage (solder pot, wave solder)
- Easily peel mask off board

Chemical Properties

For Chemical Composition, refer to MSDS.

- PHYSICAL STATE: Liquid
- ODOR: Slight
- APPEARANCE: White viscous liquid
- pH: 9.5 to 11.0
- SOLUBILITY IN WATER: Fully miscible
- DENSITY: 1.09 to 1.17 g/mL
- VISCOSITY: 9,000 to 16,000 cps

Chemical Components

CHEMICAL NAME	CAS #
Titanium Dioxide.....	13463-67-7

Application	Cure Type	Cure Time	Removal	Viscosity	Suggested Thickness	Thinner
Hand	Thermal	5 min. Ambient	Peel off. Dried mask is not soluble in liquids.	9,000-16,000 cps	15 mils	D.I. Water

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

2222-8SQ	8oz Ounce Squeeze Bottle, 24 bottles/cs
2222-G	1 Gallon in Plastic Jug, 1 jug/cs

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe

ITW Contamination Control BV
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
info@itw-cc.com

Countries Outside US

Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Techspray:](#)

[2222-8SQ](#)